



Personal Stairclimber: Outdoor

QUALITY OF LIFE IS ABOUT ENJOYING LIFE TO THE FULL, TOGETHER.

There are many reasons why somebody cannot manage stairs alone for a time, or permanently. For people with there are powered stairclimbers that are easy to use, safe and can be operated without excessive effort.

Cellar, ground floor, first floor, garden – with the Personal Stairclimber you can get your whole house back. And more: going to the doctors or post office, driving by car to visit friends and relatives, travelling by plane or train, going to the theatre or an exhibition – everything becomes much easier again.



YOUR OUTDOOR COMPANION

Thanks to its sturdy design with extra-large non-marking wheels, a braking system on the inside of the wheel rims and a wider track width, the PS Outdoor is ideal for when you are out and about. And you can easily take your PS Outdoor with you to visit friends and relatives.

| | |
|--|--|
| Load capacity for complete product including battery pack and charger | 150 kg <i>passenger weight</i> |
| Total weight | 37.7 kg |
| Weight of the heaviest part | 24.9 kg <i>climber unit with seat</i> |
| Total height | 1130 mm |
| Total width | 505 mm <i>incl. armrests</i> |
| Depth | 675 mm |
| Minimum landing space | 0.8 x 0.9 m |

Stair climbing speed: three speeds can be set at control unit

I = 10 steps per minute

II = 14 steps per minute

III = 18 steps per minute

Maximum step height: 205 to 220 mm (the maximum is achieved by tilting the stairclimber at a steeper angle)

Range per recharge depends a lot on weight of passengers and whether they are travelling up or down. However, between 300 and 500 steps can be specified as a rough guide.

If the stairclimber is in constant use, (e.g. professional mobility services) then a replacement battery pack can be fitted at any time. A mobile charger is also available to rapidly charge the battery pack during the car journey.

Battery pack voltage and capacity: 24 VDC 5.2 Ah

Protection against overloading:

- 1) Mechanical overload protection (sliding hub)
- 2) Electronic overload protection

Main wheels: non-marking grey tyres for extremely smooth operation. PT Outdoor wheels have a diameter of 260 mm (outer track width 430 mm). All other models have a diameter of 200 mm (outer track width 297 mm).

Support wheels: also feature non-marking grey tyres, are permanently braked and have a diameter of 80 mm.

